



General ordering data

| | |
|------------------|--|
| Order No. | 1960230000 |
| Part designation | LMZF 5/22/135 3.5OR |
| Version | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 22, 135°, Box |
| EAN | 4032248651115 |
| Qty. | 50 pc(s). |

System parameters

| | |
|---------------------------------|--------------------------|
| Product family | System LM |
| Conductor connection system | Tension clamp connection |
| Fitted to PCB | Soldered connection |
| Outgoing direction of conductor | 135° |
| Pitch | 5 mm |
| Pitch in inch | 0.197 inch |
| No. of poles | 22 |
| Max. adjacent poles per row | 48 |
| No. of rows | 1 |
| Solder pin length | 3.5 mm |
| Dia. of fitting hole | 1.3 mm |
| No. of solder pins per pole | 2 |
| Screwdriver blade | 0.4 x 2.5 |
| Screwdriver blade standard | DIN 5264-A |

System parameters

| | |
|---|------------------------|
| Stripping length | 6 mm |
| L1 in mm | 105 mm |
| L1 in inch | 4.134 inch |
| Electric shock protection to DIN VDE 0470 | IP 20 |
| Electric shock protection to DIN VDE 0470 | Safe from finger touch |

Material data

| | |
|---------------------------|---------------------|
| Insulating material | Wemid (PA) |
| Colour | orange |
| colour chart | Similar to RAL 2000 |
| Insulating material group | I |
| Flammability class UL 94 | V-0 |
| CTI | ≥ 600 |
| Contact base material | E-Cu |
| Contact surface | tinned |
| Storage temperature, min. | -25 °C |
| Storage temperature, max. | 55 °C |

Connectable conductors

| | |
|---|----------------------|
| Clamping range, min. | 0.13 mm ² |
| Clamping range, max. | 2.5 mm ² |
| AWG, min. | 26 |
| AWG, max. | 14 |
| Solid, min. H05(07) V-U | 0.13 mm ² |
| Solid, max. H05(07) V-U | 2.5 mm ² |
| Flexible, min. H05(07) V-K | 0.13 mm ² |
| Flexible, max. H05(07) V-K | 2.5 mm ² |
| With wire end ferrule, acc. to DIN 46 228/1, min. | 0.25 mm ² |
| With wire end ferrule, acc. to DIN 46 228/1, max. | 1.5 mm ² |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 0.25 mm ² |
| w. plastic collar ferrule, DIN 46228 pt 4, max. | 1.5 mm ² |

DIN IEC rating data

| | |
|--|-------|
| Rated current, min. No. pins (Tu=20°C) | 24 A |
| Rated current, max. No. pins (Tu=20°C) | 24 A |
| Rated current, min. No. pins (Tu=40°C) | 24 A |
| Rated current, max. No. pins (Tu=40°C) | 24 A |
| Rated voltage for overvoltage class/pollution severity II/2 | 630 V |
| Rated voltage for overvoltage class/pollution severity III/2 | 320 V |
| Rated voltage for overvoltage class/pollution severity III/3 | 250 V |
| Rated impulse withstand voltage for overvoltage class/pollution severity II/2 | 4 kV |
| Rated impulse withstand voltage for overvoltage class/pollution severity III/2 | 4 kV |
| Rated impulse withstand voltage for overvoltage class/pollution severity III/3 | 4 kV |

CSA rating data

| | |
|------------------------------------|-------|
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A |
| AWG conductor (field wiring), min. | 26 |
| AWG conductor (field wiring), max. | 14 |

UL 1059 rating data

| | |
|-----------------------------|-------|
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A |
| AWG conductor, min. | 26 |
| AWG conductor, max. | 14 |

Approvals

Approvals institutes

**Downloads**

| | |
|---------------------------------------|----------|
| CAD Library (P-CAD Format - Standard) | LMZF.lib |
|---------------------------------------|----------|

Classifications

| | |
|------------|-------------|
| ETIM 3.0 | EC001284 |
| eClass 5.1 | 27-26-11-01 |

Similar products

| Order No. | Part designation | Version |
|------------|--------------------|---|
| 1913780000 | LMZF 5/2/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 2, 135°, Box |
| 1811840000 | LMZF 5/2/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 2, 135°, Box |
| 1811950000 | LMZF 5/2/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 2, 135°, Box |
| 1812060000 | LMZF 5/2/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 2, 135°, Box |
| 1913820000 | LMZF 5/3/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 3, 135°, Box |
| 1811850000 | LMZF 5/3/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 3, 135°, Box |
| 1811960000 | LMZF 5/3/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 3, 135°, Box |

| | | |
|------------|--------------------|---|
| 1812070000 | LMZF 5/3/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 3, 135°, Box |
| 1913960000 | LMZF 5/4/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 4, 135°, Box |
| 1811860000 | LMZF 5/4/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 4, 135°, Box |
| 1811970000 | LMZF 5/4/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 4, 135°, Box |
| 1812080000 | LMZF 5/4/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 4, 135°, Box |
| 1914000000 | LMZF 5/5/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 5, 135°, Box |
| 1811870000 | LMZF 5/5/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 5, 135°, Box |
| 1811980000 | LMZF 5/5/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 5, 135°, Box |
| 1812090000 | LMZF 5/5/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 5, 135°, Box |
| 1914020000 | LMZF 5/6/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 6, 135°, Box |
| 1811880000 | LMZF 5/6/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 6, 135°, Box |
| 1811990000 | LMZF 5/6/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 6, 135°, Box |
| 1812100000 | LMZF 5/6/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 6, 135°, Box |
| 1914030000 | LMZF 5/7/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 7, 135°, Box |
| 1811890000 | LMZF 5/7/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 7, 135°, Box |
| 1812000000 | LMZF 5/7/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 7, 135°, Box |
| 1812110000 | LMZF 5/7/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 7, 135°, Box |

| | | |
|------------|---------------------|--|
| 1914040000 | LMZF 5/8/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 8, 135°, Box |
| 1811900000 | LMZF 5/8/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 8, 135°, Box |
| 1812010000 | LMZF 5/8/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 8, 135°, Box |
| 1812120000 | LMZF 5/8/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 8, 135°, Box |
| 1914050000 | LMZF 5/9/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 9, 135°, Box |
| 1811910000 | LMZF 5/9/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 9, 135°, Box |
| 1812020000 | LMZF 5/9/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 9, 135°, Box |
| 1812130000 | LMZF 5/9/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 9, 135°, Box |
| 1914070000 | LMZF 5/10/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 10, 135°, Box |
| 1811920000 | LMZF 5/10/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 10, 135°, Box |
| 1812030000 | LMZF 5/10/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 10, 135°, Box |
| 1812140000 | LMZF 5/10/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 10, 135°, Box |
| 1914080000 | LMZF 5/11/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 11, 135°, Box |
| 1811930000 | LMZF 5/11/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 11, 135°, Box |
| 1812040000 | LMZF 5/11/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 11, 135°, Box |
| 1812150000 | LMZF 5/11/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 11, 135°, Box |
| 1914090000 | LMZF 5/12/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 12, 135°, Box |

| | | |
|------------|---------------------|--|
| 1811940000 | LMZF 5/12/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 12, 135°, Box |
| 1812050000 | LMZF 5/12/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 12, 135°, Box |
| 1812160000 | LMZF 5/12/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 12, 135°, Box |
| 1960140000 | LMZF 5/13/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 13, 135°, Box |
| 1959760000 | LMZF 5/13/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 13, 135°, Box |
| 1960020000 | LMZF 5/13/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 13, 135°, Box |
| 1959880000 | LMZF 5/13/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 13, 135°, Box |
| 1960150000 | LMZF 5/14/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 14, 135°, Box |
| 1959770000 | LMZF 5/14/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 14, 135°, Box |
| 1960030000 | LMZF 5/14/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 14, 135°, Box |
| 1959890000 | LMZF 5/14/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 14, 135°, Box |
| 1960160000 | LMZF 5/15/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 15, 135°, Box |
| 1959780000 | LMZF 5/15/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 15, 135°, Box |
| 1960040000 | LMZF 5/15/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 15, 135°, Box |
| 1959900000 | LMZF 5/15/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 15, 135°, Box |
| 1960170000 | LMZF 5/16/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 16, 135°, Box |
| 1959790000 | LMZF 5/16/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 16, 135°, Box |

| | | |
|------------|----------------------|--|
| 1960050000 | LMZF 5/16/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 16, 135°, Box |
| 1959910000 | LMZF 5/16/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 16, 135°, Box |
| 1960180000 | LMZF 5/17/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 17, 135°, Box |
| 1959800000 | LMZF 5/17/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 17, 135°, Box |
| 1960060000 | LMZF 5/17/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 17, 135°, Box |
| 1959920000 | LMZF 5/17/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 17, 135°, Box |
| 1960190000 | LMZF 5/18/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 18, 135°, Box |
| 1921410000 | LMZF 5/18/135 3.5 SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 18, 135°, Box |
| 1960070000 | LMZF 5/18/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 18, 135°, Box |
| 1959930000 | LMZF 5/18/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 18, 135°, Box |
| 1960200000 | LMZF 5/19/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 19, 135°, Box |
| 1959820000 | LMZF 5/19/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 19, 135°, Box |
| 1960080000 | LMZF 5/19/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 19, 135°, Box |
| 1959940000 | LMZF 5/19/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 19, 135°, Box |
| 1960210000 | LMZF 5/20/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 20, 135°, Box |
| 1959830000 | LMZF 5/20/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 20, 135°, Box |
| 1960090000 | LMZF 5/20/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 20, 135°, Box |

| | | |
|------------|---------------------|--|
| 1959950000 | LMZF 5/20/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 20, 135°, Box |
| 1960220000 | LMZF 5/21/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 21, 135°, Box |
| 1959840000 | LMZF 5/21/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 21, 135°, Box |
| 1960100000 | LMZF 5/21/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 21, 135°, Box |
| 1959960000 | LMZF 5/21/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 21, 135°, Box |
| 1959850000 | LMZF 5/22/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 22, 135°, Box |
| 1960110000 | LMZF 5/22/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 22, 135°, Box |
| 1959970000 | LMZF 5/22/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 22, 135°, Box |
| 1960240000 | LMZF 5/23/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 23, 135°, Box |
| 1959860000 | LMZF 5/23/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 23, 135°, Box |
| 1960120000 | LMZF 5/23/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 23, 135°, Box |
| 1959980000 | LMZF 5/23/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 23, 135°, Box |
| 1960250000 | LMZF 5/24/135 3.5OR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 24, 135°, Box |
| 1959870000 | LMZF 5/24/135 3.5SW | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 24, 135°, Box |
| 1960130000 | LMZF 5/24/135 3.5GR | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 24, 135°, Box |
| 1959990000 | LMZF 5/24/135 3.5GN | PCB terminal, Tension clamp connection, Soldered connection, Clamping range, max.: 2.5 mm ² , Pitch: 5.00 mm, No. of poles: 24, 135°, Box |