

COAXIAL CONNECTOR, MMBX, 50 Ohm, Straight PCB plug (male)

81_MMBX-50-0-11/111_N

Properties

- Smallest board-to-board distance
- Very high frequencies
- Excellent return loss values
- Blind mateable
- Reliable and secure connection

**Product configuration**

Interface type	Gender	Standard
MMBX	plug	HUBER+SUHNER-MMBX

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Bronze	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PTFE / LCP	

Electrical data

Impedance	50 Ω
Interface frequency	12.4 GHz

Mechanical data

Weight	0.0023 kg
Mating cycles	100
Board mounting type	through holes
Number of printlegs	4
Height above PCB HA	9 mm
Height of stand off HS	0.6 mm
Disengagement force (to)	15 N
Engagement force max	15 N

Environmental data

Operation temperature	-55 °C ... 155°C
-----------------------	------------------

COAXIAL CONNECTOR, MMBX, 50 Ohm, Straight PCB plug (male)
81_MMBX-50-0-11/111_N

Ordering Information Table		
Item number	Item description	Packaging type
23028072	81_MMBX-50-0-11/111_NM	Tape and Reel

Additional Information	
Remarks	PCB connector with stand-offs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1369 / Date of publication: 26.11.2023 / uncontrolled copy