




由Autodesk教育版产品制作




H



RECOMMENDED PCB LAYOUT
(t=1.6mm, tol:±0.05)





RIGHT LED



3005 - 0 12 - XX

系列码
9.9H TAB UP
类别码
4.3全包带灯
流水码
11:左黄右绿GF LCP黑盘装
21:左黄右绿GF LCP黑卷装

- NOTES
- MATERIAL
- 1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
 - 2. CONTACT MATERIAL : COPPER ALLOY T=0.25MM.
 - 3. PLATING : GOLD PLATING ON CONTACT AREA AND MATTE TIN PLATING ON SOLDER AREA OVER NICKEL.
- ELECTRICAL
- 4. SHIELD : SUS T=0.20mm WITH NICKEL PLATED.
 - 5. BOTTOM SHIELD : SUS T=0.15mm .
- MECHANICAL
- 1. VOLTAGE RATING : 125 VAC RMS.
 - 2. CURRENT RATING : 1.5 AMP.
 - 3. CONTACT RESISTANCE : 40 MILLIOHMS MAX.
 - 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 100V DC .
 - 5. DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.
- ENVIRONMENTAL :
- 1. STORAGE : -40℃~+85℃.
 - 2. OPERATION : -40℃~+85℃.
1. DURRABILITY : 750 CYCLES MIN.
2. MATING/UNMATING FORCE: 2.24 KG.F MAX.



				OPERATION		SCALE		Fit	Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.35	UNIT		MM				
				X.XX	±0.25	SIZE	A4	DESIGN	赵文品2024.11.06	PART NO.	RJ45-3005-012-11	
				X.XXX	±0.05	SHEET	1/1	CHECK		TITLE	RJ45 9.9H沉板4.3全包18.64壳脚左黄右绿GF LCP黑	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	Angle	±2°	PROJ.		APPROVE		Customer No.		
				DIM	TOL							