

## Han 3HPR-C-SL-with cord-black chrome



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 003 5412
Specification	Han 3HPR-C-SL-with cord-black chrome
HARTING eCatalogue	<a href="https://b2b.harting.com/09400035412">https://b2b.harting.com/09400035412</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® HPR
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings With fixing cord

### Version

Size	3 A
Locking type	Screw locking

### Technical characteristics

Tightening torque (screw locking)	2 Nm
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Black chrome coating
Colour (hood/housing)	RAL 9005 (jet black)

## Material properties

Material (locking)	Stainless steel
RoHS	not compliant
ELV status	not compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	10
Net weight	49.3 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140057166
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors