



Pushing Performance  
Since 1945

# Han-Eco 6B-Cover-w. SL-w. cord-HTE/HSE

	Part number	19 43 006 5442
	Specification	Han-Eco 6B-Cover-w. SL-w. cord-HTE/HSE

## Identification

Category	Accessories
Series of hoods/housings	Han-Eco® B
Type of accessory	Protection cover
Description of the accessory	for hoods

## Version

Size	6 B
Locking type	Single locking lever

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

## Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



**Pushing Performance**  
Since 1945

## Material properties

Material flammability class acc. to UL 94  
(locking levers)

V-0

RoHS

compliant

ELV status

compliant

China RoHS

e

REACH Annex XVII substances

Not contained

REACH ANNEX XIV substances

Not contained

REACH SVHC substances

Not contained

California Proposition 65 substances

Not contained

Fire protection on railway vehicles

EN 45545-2 (2020-08)

Requirement set with Hazard Levels

R22 (HL 1-3)

R23 (HL 1-3)

## Specifications and approvals

Specifications

IEC 61984

EN 45545-2 Fire protection on railway vehicles

## Commercial data

Packaging size

1

Country of origin

Germany

European customs tariff number

85389099

GTIN

5713140829831

ETIM

EC002314

eCl@ss

27440208 Cap for industrial connectors