

1

2


3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	

A

A



规格 Specification:

- 1.额定值 Rating:8A 125/250VAC
- 2.接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 3.绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 4.电气寿命 Electronics life: > 10000 cycles
- 5.操作力 Operation force: $500\pm 200\text{ gf}$
- 6.所有材料符合Rohs要求 All materials are Rohs compliant

B

B





PART NO.:

SS-08 23 S G-XX N 2 X X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- ① SS: 立式拨柄开关;
② 08: 额定值8A;
③ 23: 双排三档;
④ S: 焊线端子;
⑤ G: 弧形拨柄;
⑥ XX: 拨柄高度H: 3~10mm;
⑦ N: 方形外壳;
⑧ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2;
3: 端子焊脚规格TYPE-3;
⑨ X: 拨柄颜色: B-黑色; W-白色; R-红色
⑩ X: 主体颜色: B-黑色; W-白色; R-红色

C

C



XKLB **US**

SS Series
8A 125/250VAC

产品字码标识

D

D

ANGULAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKLB

DESIGN
CHECKED
APPROVED

桑 菡

VIEW: 
UNIT: mm/in
SIZE: A4

MODEL TYPE:
SLIDE SWITCH
PART NO.:
SS-0823SG-XXN2XX
DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0

1

2

3

4