

Han-Easy Lock ® 16A, SL



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5225
Specification	Han-Easy Lock ® 16A, SL
HARTING eCatalogue	https://b2b.harting.com/09000005225

Identification

Category	Accessories
Series of hoods/housings	Han A®
Type of accessory	Locking levers

Version

Size	16 A
Locking type	Single locking lever
Han-Easy Lock®	Yes

Material properties

Material (accessories)	Polycarbonate (PC) Stainless steel
Colour (accessories)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Commercial data

Packaging size	10
Net weight	12 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140002302
ETIM	EC002939
eCl@ss	27440392 Connector (accessories)