

Pushbutton Ø 19 mm silver contact

82-5551.2000



<https://eao.com/p/82-5551.2000>

Your product:



82-5551.2000

Pushbutton Ø 19 mm silver contact

FRONT

Front dimension: Ø 22 mm

Front bezel material: Aluminium

Front bezel shape: flush

Front form: round

MOUNTING

Mounting cut-out: Ø 19 mm

Mounting type: Panel mounting

OPERATING-/INDICATION PART

Lens optics: opaque

Lens material: Aluminium

Lens colour: Nature

Lens illumination: non illuminative

Lens shape: flush

ELECTRICAL CHARACTERISTICS

Thermal current I_{th}: 5 A

Switching voltage and switching current:

according to IEC 60947-5-1 (Silver contacts)	
Service categorie AC-15	
Voltage	Current
24 VAC	1 A
35 VAC	1 A (M12 version)
110 VAC	1 A
220 VAC	0.5 A
Switch rating DC service categorie DC-13 (Silver contacts)	
Voltage	Current
24 VDC	0.7 A
35 VDC	0.5 A (M12 version)
110 VDC	0.2 A
220 VDC	0.1 A

according to UL 508 (Silver contacts)	
cosφ 0,75 ... 0,8	
Voltage	Current
120 VAC	5 A
240 VAC	3 A
24 VAC	1 A

Pollution degree:	2, according to EN IEC 60947-1
Contacts:	1 C
Rated Operational Voltage Ue:	250 VAC
Rated insulation voltage Ui:	250 V
Electric strength:	1500 VAC, 50 Hz 1 minute between life terminals and ground
Electrical lifetime:	50 000 cycles of operation

MECHANICAL CHARATERISTIC

Tightening torque:	0.5 ... 0.6 Nm
Weight:	0.018 kg
Contact material:	Silver
Operating Travel:	ca. 3 mm
Terminal:	Soldering terminal, 2.8 x 0.5 mm
Switching system:	Snap-action switching element
Mechanical lifetime:	500 000 cycles of operation
Switching action:	Maintained
Operating force:	4 N ... 7 N

AMBIENT CONDITION

Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6
IP front protection:	IP65, IP67
Storage temperature:	

– 40 °C ... + 80 °C

Shock resistance:

Max. 500 m / s² as per IEC 60068-2-27

Operating temperature:

– 30 °C ... + 70 °C

Climate resistance:

Damp heat, 21 days according to IEC 60512-11

CERTIFICATE

RoHS:

RoHS compliant

REACH:

REACH compliant

Approbations:

CB, CCC, C UL, UL

Conformities:


CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

OTHER


Short Description:

Pushbutton Ø 19 mm silver contact, Maintained, 1 C, Soldering terminal, 2.8 x 0.5 mm, round, Aluminium, Nature


Mounting cut-outs:




Component layouts:



Wiring diagrams:



Dimension drawings:



A = Solder terminal
B = Screw terminal