

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE3-710077	2006/12/18	DongYaLi	Move O-Ring To ZSE00100715
C	LEN1390191	2013/09/02	Lu Di	Update Dimension



F




E

D



C

B


A



With Liquid Glue
點防水膠




- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate : IP68
IP68: 1M of depth of water 24 hours
(防水等級 : IP68)
(IP68: 1米水深24小時)
 - * Do Mating Test After Glued
點膠後, 須作對插測試
 - * HD-SUB Conn. : Black Core, PBT
 - * Plastic Jacket : Black, Nylon+GF
 - * Pin: Copper Alloy, Gold Plated
 - * Ring: Light Blue, Silicone
 - * Screw: Copper Alloy, Nickel Plated, #4-40 UNC
 - * The 90° Board Lock Needs To Connect The Iron Shell
L型支架需接鐵殼




Screw L=5.0 For Panel Thickness
Under 1.2mm
適用板厚為 1.2mm以下

Screw L=6.0 For Panel Thickness
Between 1.2~2.0mm
適用板厚為 1.2~2.0mm



Recommended Panel Cut-Out
建議挖孔尺寸



15 Pin Male Conn.
PCB Pin Layout

Max. Distance From The
Circuit Board Edge
距離 PCB 板邊尺寸

UNIT: mm		TITLE	HDI5/M Conn, Panel, PCB 90° Add Board Lock		
TOLERANCE		SCALE	SIZE	SHEET	OF
.X ±0.25		1:1	A4	1	1
.XX ±0.1		REV.	WC-REV.		
.XXX ±0.05		C	A.3		
ANGLES ±1°		$\varnothing$ Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	HDB-15PMMP-SB8001	DRAWN BY	Di_lu	DATE	2013/09/02
DWG NO	HDB-15PMMP-SB8001	CHECKED BY	Mafei	DATE	2013/09/02
CUSTOMER	ALTW	APPROVED BY	Victor	DATE	2013/09/02