



Pushing Performance  
Since 1945

# Han-Easy Lock ® 32A, DL



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5223
Specification	Han-Easy Lock ® 32A, DL
HARTING eCatalogue	<a href="https://b2b.harting.com/09000005223">https://b2b.harting.com/09000005223</a>

## Identification

Category	Accessories
Series of hoods/housings	Han A®
Type of accessory	Locking levers

## Version

Size	32 A
Locking type	Double locking lever
Han-Easy Lock®	Yes

## Material properties

Material (accessories)	Polycarbonate (PC) Stainless steel
Colour (accessories)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel



Pushing Performance  
Since 1945

Material properties

Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Commercial data

Packaging size	10
Net weight	17 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140002289
ETIM	EC002939
eCl@ss	27440392 Connector (accessories)