

NEW ENGLAND SEMICONDUCTOR

SMALL SIGNAL DUAL PNP TRANSISTOR TO-78

PACKAGE	DEVICE TYPE	V _{CEO} (sus) VOLTS	I _C (max) AMPS	h _{FE} @ I _C /V _{CE} min/max @ mA/V	V _{CE(sat)} @ I _C /I _B V @ mA/mA	C _{QB} pF	f _T (MHz)
TO-78 	2N3726	45	0.1	115@50/5	0.25@50/2.5	8	200
	2N3727	45	0.1	115@50/5	0.25@50/2.5	8	200
	2N3806	60	0.05	150/450@0.5/5	0.25@1/0.1	4	100
	2N3807	60	0.05	300/900@0.5/5	0.25@1/0.1	4	100
	2N3808	60	0.05	150/450@0.5/5	0.25@1/0.1	4	100
	2N3809	60	0.05	300/900@0.5/5	0.25@1/0.1	4	100
	2N3810	60	0.05	150/450@0.5/5	0.25@1/0.1	4	100
	2N3810A	60	0.05	150/450@0.5/5	0.25@1/0.1	4	100
	2N3811	60	0.05	300/900@0.5/5	0.25@1/0.1	4	100
	2N3811A	60	0.05	300/900@0.5/5	0.25@1/0.1	4	100
	2N4015	60	0.3	135/350@1/5	0.25@50/2.5	8	200
	2N4016	60	0.3	135/350@1/5	0.25@50/2.5	8	200
	2N4854^	40	0.6	100/300@150/10	0.4@150/15	8	200
	2N4855	40	0.6	40/120@150/10	0.4@150/15	8	200
	2N4937	40	0.05	50/250@10/10	-	5	300
	2N4938	40	0.05	50/250@10/10	-	5	300
	2N4939	40	0.05	50/250@10/10	-	5	300
	2N5795^	60	0.6	40/120@150/10	0.4@150/15	8	200
	2N5796^	60	0.6	100/300@150/10	0.4@150/15	8	200

^Available in JAN, JANTX, JANTXV