




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2016-05-09	Spring	Change Rev.01 To Rev.A




Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP68(Mated, 1M/24hr)
- * Working Voltage Rating:
Power AC/DC 300V
Data DC 30V
- * Working Current:
Power: 10A
Data: 05A
- * Housing: Nylon+GF, Black
- * Pins: Copper Alloy, Gold & Ni Plated
- * Cable: UL21996 3C*16AWG+(26#*2P+D+AL)+F+AL/MY, PVC Jacket, OD=11.0, Black.
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

CBD-08AMMM-QL8FXX

XX :01~99Meters
01 :01Meter
02 :02Meters
:
:
:
99 :99Meters



8	Drain (26AWG) 地線
7	Blue (26AWG) 藍
6	Red (26AWG) 紅
5	Green (26AWG) 綠
4	White (26AWG) 白
3	Black (16AWG) 黑
2	Green (16AWG) 綠
1	White (16AWG) 白
Conn.	Wire Color
Pin Out	

Twist
對線
Twist
對線

UNIT:mm
TOLERANCE
±0.5

TITLE X-Lok C Size Cable Molding 8Pin M Connector M Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.1	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Spring	DATE 2016-05-09
DWG NO CBD-08AMMM-QL8FXX	CHECKED BY Fisher	DATE 2016-05-09
CUSTOMER ALTW	APPROVED BY Kevin	DATE 2016-05-09

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.