

## Cable Sealing M25x1,5 metal 10.5 - 14mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 12 000 5057
Specification	Cable Sealing M25x1,5 metal 10.5 - 14mm
HARTING eCatalogue	<a href="https://b2b.harting.com/19120005057">https://b2b.harting.com/19120005057</a>

### Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for hoods

### Technical characteristics

Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	28
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP65
Size	M25
Clamping range	10.5 ... 14 mm

### Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	10
Net weight	25 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140124011
ETIM	EC003608
eCl@ss	27140807 Additional components cable gland