

Coaxial Cable Connector 16_C-50-3-3/133_N

Description

Right angle cable plug

Interface standards

IEC 60169-7_MIL-STD-348A/302



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0551 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00006033
Catalogue drawing	DCA-00198825
Assembly instruction	DOC-0000179246

Ordering Information

Single package	16_C-50-3-3/133_NE
----------------	--------------------

Additional Information

Suitable cables	RG_223_/U, RG_142_B/U
-----------------	-----------------------