










With Liquid Glue



Pin Assignments
Front View




Recommended Panel Cut-out



Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP68
- * Working Voltage Rating: AC 300 V
- * Working Current Rating: 5A
- * Flame Class: UL94V-0 (UV Resistance)
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Nut: Nylon+GF, Black
- * Gasket: Silicone, Gray
- * Panel Thickness Max: 4.5mm

UNIT:mm



TOLERANCE
.X ±0.25

TITLE

X Lok B-Size
Receptacle M Conn M 8 Pin

SCALE
2:1

SIZE
A4

SHEET
1 OF 1

REV.
A

WC-REV.
A.1

$\varnothing$ Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

BD-08RMMS-QC8001

DWG NO

BD-08RMMS-QC8001

CUSTOMER

ALTW

DRAWN BY

Micky

CHECKED BY

Spring

APPROVED BY

Kevin

DATE

2014-10-24

DATE

2014-10-24

DATE

2014-10-24