

Pushbutton Ø 19 mm silver contact

82-5162.2000



<https://eao.com/p/82-5162.2000>

Your product:



82-5162.2000
Pushbutton Ø 19 mm silver contact

FRONT

Front bezel material:	Stainless steel
Front bezel shape:	flush
Front dimension:	Ø 22 mm
Front form:	round

MOUNTING

Mounting cut-out:	Ø 19 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens illumination:	non illuminative
Lens colour:	Silver
Lens material:	Stainless steel
Lens shape:	raised
Lens optics:	opaque

ELECTRICAL CHARACTERISTICS

Thermal current Ith:	5 A
Rated Operational Voltage Ue:	250 VAC
Switching voltage and switching current:	

according to IEC 60947-5-1 (Silver contacts)

Service categorie AC-15

Voltage	Current
24 VAC	1 A
35 VAC	1 A (M12 version)
110 VAC	1 A
220 VAC	0.5 A

Switch rating DC service categorie DC-13 (Silver contacts)

Voltage	Current
24 VDC	0.7 A
35 VDC	0.5 A (M12 version)
110 VDC	0.2 A
220 VDC	0.1 A

according to UL 508 (Silver contacts)

$\cos\phi$ 0,75 ... 0,8

Voltage	Current
120 VAC	5 A
240 VAC	3 A
24 VAC	1 A

Electrical lifetime: 50 000 cycles of operation

Contacts: 1 C

Electric strength: 1500 VAC, 50 Hz 1 minute between life terminals and ground

Pollution degree: 2, according to EN IEC 60947-1

Rated insulation voltage Ui: 250 V

MECHANICAL CHARACTERISTIC

Switching system: Snap-action switching element

Tightening torque: 0.5 ... 0.6 Nm, Screw terminal 0.1 Nm

Mechanical lifetime: 500 000 cycles of operation

Contact material: Silver

Terminal: Screw terminal

Operating Travel: ca. 3 mm

Weight: 0.02 kg

Switching action: Maintained

Operating force: 4 N ... 7 N

AMBIENT CONDITION

IP front protection: IP65, IP67

Storage temperature: - 40 °C ... + 80 °C

Climate resistance: Damp heat, 21 days according to IEC 60512-11

Vibration resistance:

10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6

Operating temperature: – 30 °C ... + 70 °C

Shock resistance: Max. 500 m / s² as per IEC 60068-2-27

CERTIFICATE

Conformities: CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

Approbations: CB, CCC, C UL, UL


REACH: REACH compliant

RoHS: RoHS compliant

OTHER


Short Description: Pushbutton Ø 19 mm silver contact, Maintained, 1 C, Screw terminal, round, Stainless steel, Silver

Dimension drawings:




A = Solder terminal
B = Screw terminal

Mounting cut-outs:



Component layouts:



Wiring diagrams:

