



Pushing Performance
Since 1945

Han F+B cover-HTE blue



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 513 5411
Specification	Han F+B cover-HTE blue
HARTING eCatalogue	https://b2b.harting.com/09155135411

Identification

Category	Accessories
Series	Han® F+B
Type of accessory	Protection cover
Description of the accessory	for hoods

Version

Locking type	Screw locking
Details	<p>Cleaning: For cleaning with high pressure lances, a cleaning distance > 30 cm is recommended in order to avoid mechanical damage to the connector's exterior parts.</p> <p>Strain relief: A suitable strain relief is required to enable the F+B connector to resist the stress caused e.g. by the daily cleaning of the machinery. DIN VDE 0100-520: 2013-06 defines the stress relief for a connector depending on the outer diameter of the cable.</p>

Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP67 locked condition IP6K9K acc. to ISO 20653

Material properties

Material (hood/housing)	Polypropylen
Roughness of the surface	≤1.12 µm
Colour (hood/housing)	Blue
Material (seal)	Silicone



Pushing Performance
Since 1945

Material properties

Colour (seal)	Blue
Material flammability class acc. to UL 94	HB
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
EG1935/2004	compliant
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

Specifications and approvals

Approvals	Ecolab Topactive 200
	Ecolab Topactive 500
	Ecolab Topax 66
	Ecolab Topactive OKTO
	Ecolab Topax 990
	FDA 21 CFR 177.1520
	FDA 21 CFR 177.2600

Commercial data

Packaging size	1
Net weight	13.9 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140192331
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors