

## Han-Eco cable gland M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 000 5141
Specification	Han-Eco cable gland M40
HARTING eCatalogue	<a href="https://b2b.harting.com/19410005141">https://b2b.harting.com/19410005141</a>

### Identification

Category	Accessories
Series of hoods/housings	Han-Eco®
Type of accessory	Cable gland

### Technical characteristics

Tightening torque	20 Nm Fitting 20 Nm Cap nut
Wrench size	46
Limiting temperature	-40 ... +125 °C
Size	M40
Clamping range	16 ... 28 mm

### Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



**Pushing Performance**  
Since 1945

## Commercial data

Packaging size	2
Net weight	61.9 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140130548
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)