



Pushing Performance  
Since 1945

# Han-Eco 10B-Outd-Cov-w.DL-w.cord-HTE/HSE

	Part number	19 43 210 5422
	Specification	Han-Eco 10B-Outd-Cov-w.DL-w.cord-HTE/HSE

## Identification

Category	Accessories
Series of hoods/housings	Han-Eco® B
Type of accessory	Protection cover
Description of the accessory	for hoods

## Version

Size	10 B
Locking type	Double locking lever

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

## Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



**Pushing Performance**  
Since 1945

## Material properties

Material flammability class acc. to UL 94  
(locking levers)

V-0

RoHS

compliant

ELV status

compliant

China RoHS

e

REACH Annex XVII substances

Not contained

REACH ANNEX XIV substances

Not contained

REACH SVHC substances

Not contained

Fire protection on railway vehicles

EN 45545-2 (2020-08)

Requirement set with Hazard Levels

R22 (HL 1-3)  
R23 (HL 1-3)

## Specifications and approvals

Specifications

IEC 61984  
EN 45545-2 Fire protection on railway vehicles

## Commercial data

Packaging size

1

Net weight

69 g

Country of origin

Germany

European customs tariff number

85389099

GTIN

5713140829688

ETIM

EC002314

eCl@ss

27440208 Cap for industrial connectors