

## Han 6M-Metal Cover-f. Coupler



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Accessories
Series of hoods/housings	Han® M
Type of accessory	Protection cover
Description of the accessory	for cable to cable housing Metal

### Version

Size	6 B
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	45.8 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140055421
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors