

Han TC100-HMC-FC-CRT-10 mm²-AU



Part number	09 11 200 6214
Specification	Han TC100-HMC-FC-CRT-10 mm ² -AU
HARTING eCatalogue	https://b2b.harting.com/09112006214

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Series	TC 100
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	10 mm ²
Rated current	≤100 A
Contact resistance	≤0.3 mΩ
Stripping length	19 mm
Limiting temperature	-40 ... +125 °C
Mating cycles with other HMC components	≥10,000

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	HMC gold plated

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	10
Net weight	11 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188273
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors