

## Han PushPull PFT metal rectangular HIFF



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 012 0311
Specification	Han PushPull PFT metal rectangular HIFF
HARTING eCatalogue	<a href="https://b2b.harting.com/09350120311">https://b2b.harting.com/09350120311</a>

### Identification

Category	Connectors
Series	Han® PushPull (V14)
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	for rectangular panel cut out

### Version

Locking type	PushPull
--------------	----------

### Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

## Specifications and approvals

Specifications	IEC 61076-3-117
	EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	21 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140053915
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors