


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1350287	2013/05/31	Yulong	Update the Dimension
C	LEN13B0246	2013/11/12	SAM	Modify Dimension.
D	LEN1740001	2017/04/17	Gaotong	Correct tolerance




Screw L=5.0 For Panel Thickness Under 1.2mm
適用板厚為1.2mm 以下


Screw L=6.0 For Panel Thickness Between 1.2~2.0mm
適用板厚為1.2~2.0mm



- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate : IP67
 - * Do Mating Test After Glued
點膠後，須作對插測試
 - * D-SUB Conn. : Black Core,PBT
 - * Plastic Jacket : Black,Nylon+GF
 - * Male Pin : Copper Alloy , Gold Plated
 - * Ring : Light Blue,Silicone
 - * Screw : Copper Alloy,Nickel Plated, #4-40 UNC
 - * The 180° Board Lock Needs To Connect The Iron Shell
180° 型支架需接鐵殼



Recommended Panel Cut-Out
建議挖孔尺寸



UNIT:mm		TITLE	D-Sub Conn. 37 Pins PCB Type For Panel,PCB 180° Board Lock		
TOLERANCE		SCALE	4:5	SIZE	A4
.X ± 0.25		REV.	D	WC-REV.	B.2
.XX ± 0.1					
.XXX ± 0.05					
ANGLES $\pm 1^\circ$					

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	SDB-37PMMP-SA7001	DRAWN BY	Gaotong	DATE	2017/04/17
DWG NO	SDB-37PMMP-SA7001	CHECKED BY	Kris	DATE	2017/04/17
CUSTOMER	ALTW	APPROVED BY	Max	DATE	2017/04/17

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.