



Pushing Performance  
Since 1945

# Han D F Crimpkontakt 0,14-0,37mm<sup>2</sup> GT/SMC



|               |  |
|---------------|--|
| Part number   | 09 15 000 6404                                       |
| Specification | Han D F Crimpkontakt 0,14-0,37mm <sup>2</sup> GT/SMC |

## Identification

|                 |                    |
|-----------------|--------------------|
| Category        | Contacts           |
| Series          | Han D <sup>®</sup> |
| Type of contact | Crimp contact      |

## Version

|                       |                 |
|-----------------------|-----------------|
| Gender                | Female          |
| Manufacturing process | Turned contacts |

## Technical characteristics

|                         |                               |
|-------------------------|-------------------------------|
| Conductor cross-section | 0.14 ... 0.37 mm <sup>2</sup> |
| Conductor cross-section | AWG 26 ... AWG 22             |
| Rated current           | ≤10 A                         |
| Contact resistance      | ≤3 mΩ                         |
| Stripping length        | 8 mm                          |

## Material properties

|                             |  |
|-----------------------------|--|
| Material (contacts)         | Copper alloy   |
| Surface (contacts)          | Han <sup>®</sup> -GoldTec                              |
| RoHS                        | compliant with exemption                               |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                               |
| China RoHS                  | 50   |
| REACH Annex XVII substances | Not contained  |
| REACH ANNEX XIV substances  | Not contained  |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | b51e5b97-eeb5-438b-8538-f1771d43c17d |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead                                 |

## Specifications and approvals

|                |             |
|----------------|-------------|
| Specifications | IEC 60664-1 |
|                | IEC 61984   |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 100  |
| Net weight                     | 0.6 g                                      |
| Country of origin              | Germany                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140022362                              |
| ETIM                           | EC000796                                   |
| eCl@ss                         | 27440204 Contact for industrial connectors |