

## Han CGM-P M25x1,5 D.9-16mm grey



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5190
Specification	Han CGM-P M25x1,5 D.9-16mm grey
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005190">https://b2b.harting.com/19000005190</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® CGM-P
Type of accessory	Cable gland

### Technical characteristics

Tightening torque	≤5 Nm (depending on the cable and the seal insert used)
Wrench size	33
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M25
Clamping range	9 ... 16 mm
Width across corners	33.5 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 7035 (light grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No

## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 514B QCRV.E479780 CSA-C22.2 No. 18.3 QCRV7.E479780

## Commercial data

Packaging size	10
Net weight	23.5 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27144432 Screwed cable gland (electr.)