





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



ALTW
CONFIDENTIAL
2016-07-14
R&D DEPT.



ALTW
DCC. DEPT.
CONFIDENTIAL
2016.07.18
ISSUED



- Note:
- * ϕ Important Dimension To Check.
 - * Waterproof Rate: IP68(Unmated)
In 1 meter water within 24 hours
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: 10A
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Nut: Nylon+GF, Black
 - * Gasket: Silicone, Gary
 - * Use Without Waterproof Cap
Panel Thickness Max: 4.0mm
 - * Use With Waterproof Cap
Panel Thickness Max: 3.0mm



UNIT:mm

TOLERANCE
.X ± 0.25

TITLE X Lok B-Size Receptacle Front Fastened M Conn M 2 Pin			
SCALE 2:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.1	ϕ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO BB-02PMMS-QC800P	DRAWN BY Wes Fan	DATE 2016-07-14
DWG NO BB-02PMMS-QC800P	CHECKED BY Spring Liu	DATE 2016-07-14
CUSTOMER ALTW	APPROVED BY Kevin Hu	DATE 2016-07-14