


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1580041~042	2015-07-26	Yulong_wang	Change to Share Drawing.



M 12B - 05 P M M P - S F 8 XXX

12B: B-Code
05: 5Pin
P: Panel (板端)
M: Male Connector (公座)
M: Male Pin (公Pin)
P: PCB THT/DIP Type (180° 基板插件式)

001: PG9
002: M16*1.5
8: IP68 (防水等級68)
F: Front Fasten (前鎖式/Enclosure Rear Mount)
S: Screw (螺紋式)



- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP68.
 - * Housing: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Shield: Zinc Alloy, Nickel Plated.
 - * Screw Nut: Zinc Alloy, Nickel Plated.
 - * Panel O-Ring: Viton, Black.
 - * Rated Voltage: 60V dc. or ac.
 - * Rated Current: 4A
 - * Operating Temperature: -40~105°C
 - * For Panel Thickness Max 4.5mm.
 - * Recommended Nut Torque: 4-6 Kgf.cm.

A	UNIT:mm		TITLE M12 B-Code Male Conn. PCB Type Unshielded			ITEM NO		DRAWN BY Yulong_wang		DATE 2015-07-26	
	TOLERANCE		SCALE 2:1	SIZE A4	SHEET 1 OF 1	DWG NO M12B-05PMMP-SF8XXX		CHECKED BY Cary		DATE 2015-07-26	
	.X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		REV. B	WC-REV. A.5	$\varnothing$: Inspection item	CUSTOMER ALTW		APPROVED BY Jerry		DATE 2015-07-26	
			Amphenol LTW 安費諾亮泰企業股份有限公司							8 FMW10702-01-02A1	