

## Han 10B-gs-ZV-M25



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 30 010 0586  |
| Specification      | Han 10B-gs-ZV-M25   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19300100586">https://b2b.harting.com/19300100586</a> |

### Identification

|                          |                    |
|--------------------------|--------------------|
| Category                 | Hoods/Housings     |
| Series of hoods/housings | Han <sup>®</sup> B |
| Type of hood/housing     | Hood               |
| Type                     | High construction  |

### Version

|                         |   |
|-------------------------|---|
| Size                    | 10 B  |
| Version                 | Side entry  |
| Number of cable entries | 1   |
| Cable entry             | 1x M25  |
| Locking type            | Central locking lever (on the hood)               |
| Field of application    | Standard hoods/housings for industrial connectors |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Mating cycles                          | ≥500   |
| Degree of protection acc. to IEC 60529 | IP65   |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12                                  |

### Material properties

|                         |                    |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
|-------------------------|--------------------|



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                            |
|--------------------------------------|----------------------------|
| Surface (hood/housing)               | Powder-coated              |
| Colour (hood/housing)                | RAL 7037 (dust grey)       |
| Material (locking)                   | Stainless steel            |
| RoHS                                 | compliant                  |
| ELV status                           | compliant                  |
| China RoHS                           | e                          |
| REACH Annex XVII substances          | Not contained              |
| REACH ANNEX XIV substances           | Not contained              |
| REACH SVHC substances                | Not contained              |
| California Proposition 65 substances | Yes                        |
| California Proposition 65 substances | Nickel                     |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)       |
| Requirement set with Hazard Levels   | R1 (HL 1-3)<br>R7 (HL 1-3) |

## Specifications and approvals

|           |              |
|-----------|--------------|
| Approvals | CE<br>DNV GL |
|-----------|--------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 308.68 g                                 |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140125483                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |