


DESCRIPTION: M12 MALE - CABLE MOUNT - 4 POS.

SPECIFICATIONS:




MATERIALS:
HOUSING: PBT, UL94 V-0, BLACK
CONTACTS: GOLD PLATED BRASS (SEE P/N KEY BELOW)
NUT: (SEE P/N KEY BELOW)
ORING: EPDM, BLACK

ELECTRICAL:
RATED CURRENT: 4A
RATED VOLTAGE: 250V
INSULATION RESISTANCE: 100 MOhms MIN.
CONTACT RESISTANCE: 10 mOhms MAX.


ENVIRONMENT:
OPERATING TEMPERATURE: -40°C TO +85°C
WATER PROOF: IP67
MAX WIRE AWG: 20



NUT



858-004-103RLUY
3 = BRASS/NICKEL NUT
S = STAINLESS STEEL NUT
1 = GOLD FLASH
4 = 10µ" GOLD



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON
DATE: 03/07/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 1 OF 1	REV 5
DWG NO.	858-004-103RLUY	