

6





5

4

3

2

1



SPECIFICATIONS:

Housing: PA66, UL-94V-0 rated

Contacts: Copper alloy

Ratings: 3A, 120VAC

1.3A, 277VAC

1.04A, 347VAC

0.75A, 480VAC

Applicable wire: Line:12 - 14AWG, Load:18AWG

solid or Tin bonded stranded

Wire Strip length: 9~10mm


Max. operating temperature: 105°C

Certifications:

UL2459 "Touch safe" 

CSA 22.2/2459

Meets NEC 410.73(G) & CEC 30-308 (4)



REVISIONS
CHANGE
CHKNG
CHECK
APPR
REV
DATE

TOLERANCE UNLESS OTHERWISE SPECIFIED	
X	± 1
X.X	± 0.4
X.XX	± 0.13
DRAWN BY	PB
CHECK BY	
APPR BY	
DATE:	11/16/17

Power Dynamics, Inc.	
Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076	
PART: LUMINAIRE DISCONNECTOR 2X2 TYPE	
PART #: PD-CN-01	
SIZE: A	ALL DIMENSIONS FOR REFERENCE ONLY DIMENSIONS ARE IN MILLIMETERS
SCALE: NTS	REV:

SHEET
1 of 1

6

5

4

3

2

1