



Part No	Pin	A	B	C
WAFER-254W-2P	2	2.50	10.00	8.30
WAFER-254W-3P	3	5.00	12.50	10.80
WAFER-254W-4P	4	7.50	15.00	13.30
WAFER-254W-5P	5	10.00	17.50	15.80
WAFER-254W-6P	6	12.50	20.00	18.30
WAFER-254W-7P	7	15.00	22.50	20.80
WAFER-254W-8P	8	17.50	25.00	23.30
WAFER-254W-9P	9	20.00	27.50	25.80
WAFER-254W-10P	10	22.50	30.00	28.30
WAFER-254W-11P	11	25.00	32.50	30.80
WAFER-254W-12P	12	27.50	35.00	33.30
WAFER-254W-13P	13	30.00	37.50	35.80
WAFER-254W-14P	14	32.50	40.00	38.30
WAFER-254W-15P	15	35.00	42.50	40.80
WAFER-254W-16P	16	37.50	45.00	43.30

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 3A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: WAFER 2.5 贴片
			PAR: WAFER-254W-NP
DECIMALS:	ANGLES:	CUSTOMER COPY	DWN:
X.:±0.2	X':.:±5°		CHKD:
.X.:±0.1	X.X':.:±3°		APVD:
.XX.:±0.05	X.XX':.:±1°		SCALE:1:1
		SIZE:A4	SHEET:1F1
			REV:A