









| Part No        | Pin | A     | B     |
|----------------|-----|-------|-------|
| WAfer-200L-2P  | 2   | 2.00  | 8.00  |
| WAfer-200L-3P  | 3   | 4.00  | 10.00 |
| WAfer-200L-4P  | 4   | 6.00  | 12.00 |
| WAfer-200L-5P  | 5   | 8.00  | 14.00 |
| WAfer-200L-6P  | 6   | 10.00 | 16.00 |
| WAfer-200L-7P  | 7   | 12.00 | 18.00 |
| WAfer-200L-8P  | 8   | 14.00 | 20.00 |
| WAfer-200L-9P  | 9   | 16.00 | 22.00 |
| WAfer-200L-10P | 10  | 18.00 | 24.00 |
| WAfer-200L-11P | 11  | 20.00 | 26.00 |
| WAfer-200L-12P | 12  | 22.00 | 28.00 |
| WAfer-200L-13P | 13  | 24.00 | 30.00 |
| WAfer-200L-14P | 14  | 26.00 | 32.00 |
| WAfer-200L-15P | 15  | 28.00 | 34.00 |
| WAfer-200L-16P | 16  | 30.00 | 36.00 |

## NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

## SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

| MANUFACTURE DWG                       |           |  东莞市讯普电子科技有限公司<br>DongGuan XunPu Electronics Co.,Ltd |                         |
|---------------------------------------|-----------|-------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|
| UNLESS OTHERWISE SPECIFIED TOLERANCES |           |                                                      | TITLE:<br>WAfer 2.00 立贴 |
|                                       |           |                                                                                                                                           | PAR<br>WAfer-200L-NP    |
|                                       |           |                                                                                                                                           | DWN                     |
|                                       |           |                                                                                                                                           | CHKD                    |
| DECIMALS:                             | ANGLES:   |                                                                                                                                           | APVD                    |
| X.:±0.2                               | X'':±5°   |                                                                                                                                           | SCALE:1:1               |
| .X:±0.1                               | X.X':±3°  |                                                                                                                                           | UNIT:MM                 |
| .XX:±0.05                             | X.XX':±1° |                                                                                                                                           | SIZE:A4                 |
| CUSTOMER COPY                         |           | SIZE:A4                                                                                                                                   | SHEET:1F1               |
|                                       |           |                                                                                                                                           | REV:A                   |