








THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP67.
 - * Housing: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Shield: Zinc Alloy, Nickel Plated.
 - * Screw Nut: Copper Alloy, Nickel Plated.
 - * O-Ring1: Viton, Green.
 - * O-Ring2: EPDM, Black.
 - * For Panel Thickness Max 4.5mm.
 - * Nut Torque: 4~6 kgf.cm.

UNIT:mm				TITLE		M8 5Pin Panel F Conn. F Pin Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY		DATE			
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE		SIZE				SHEET		OF		CHECKED BY		DATE	
		3:1		A4				1		1		Jimmy		2014-01-10	
		REV.		WC-REV.		QC: Inspection item		CUSTOMER		APPROVED BY		DATE			
		A		A.1				ALTW		Jerry		2014-01-10			
1		2		3		4		5		6		7		8 FMM10702-01-02A	