

Han Snap Plastic Housing Size 16B



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 016 0401
Specification	Han Snap Plastic Housing Size 16B
HARTING eCatalogue	https://b2b.harting.com/09330160401

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Snap®
Type of hood/housing	Shell housing

Version

Size	16 B
Version	Top/side entry
Locking type	Snap-in latches
Details	Size 16 A by using the corresponding adapter!
Pack contents	2 half shells with blind plugs

Technical characteristics

Tightening torque	0.8 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Retention force	≥300 N locked condition

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60068-2-6 Vibration (sinusoidal)
	IEC 60068-2-27 Shock

Commercial data

Packaging size	1
Net weight	48 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140051287
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors