






3D Drawing



Part No	Pin	A	B	C	D
FPC-0.5FX-4PWBH10	4	3.77	1.50	2.60	3.27
FPC-0.5FX-5PWBH10	5	4.27	2.00	3.10	3.77
FPC-0.5FX-6PWBH10	6	4.77	2.50	3.60	4.27
FPC-0.5FX-8PWBH10	8	5.77	3.50	4.60	5.27
FPC-0.5FX-10PWBH10	10	6.77	4.50	5.60	6.27
FPC-0.5FX-12PWBH10	12	7.77	5.50	6.60	7.27
FPC-0.5FX-14PWBH10	14	8.77	6.50	7.60	8.27
FPC-0.5FX-15PWBH10	15	9.27	7.00	8.10	8.77
FPC-0.5FX-16PWBH10	16	9.77	7.50	8.60	9.27
FPC-0.5FX-18PWBH10	18	10.77	8.50	9.60	10.27
FPC-0.5FX-20PWBH10	20	11.77	9.50	10.60	11.27
FPC-0.5FX-22PWBH10	22	12.77	10.50	11.60	12.27
FPC-0.5FX-24PWBH10	24	13.77	11.50	12.60	13.27
n	n	n*0.5+1.77	(n-1)*0.5	n*0.5+0.6	n*0.5+1.27

NOTES:

1. MATERIAL:



HOUSING: HIGH-TEMP PLASTIC,UL 94-V0,COLOR:WHITE;
COVER: HIGH-TEMP PLASTIC,UL 94-V0,COLOR:BROWN;
CONTACT: COPPER ALLOY;
LEG: COPPER ALLOY;

2. PLATING:


CONTACT: GOLD OR TIN PLATED ON NICKEL OVERALL.
LEG: TIN PLATED ON NICKEL OVERALL.

3. RATING:

CURRENT RATING: 0.4A AC/DC
VOLTAGE RATING: 50V AC/DC
TEMPERATURE RANGE: -55°C~+85°C;



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 0.5Pitch 1.0H ZIF/插线式
			PAR FPC-0.5FX-NPWBH10
			DWN
			CHKD
			APVD
DECIMALS:	ANGLES:		SCALE1:1 UNIT:MM
.X:±0.30	.X':±5°		SIZE:A4
.XX:±0.20	.XX':±2°		SHEET:1F1
.XXX:±0.05	.XXX':±1°		REV:A
CUSTOMER COPY			




SCALE 1:4

PIN NO.	W	C	PCS /REEL	REEL/CARTON	SUM(PCS)
04PIN~15PIN	16	—	5000	13	65000
16PIN~30PIN	24	—	5000	10	50000
31Pin~40PIN	32	28.4	5000	7	35000
50PIN	44	38.4	5000	5	25000

NOTE:

- 1.10 Sprocket hole pitch cumulative tolerance ± 0.20 .
- 2.Carrier camber is within 1mm in 100mm.
- 3.Material: black conductive polystyrene alloy.
- 4.Material Thickness: 0.3 ± 0.05 mm.
- 5.All dimensions meet EIA-481-B requirements.
- 6.5000pcs Pef Reel.
- 7.For tape width(dim W)16 and 24mm pilot holes are provided on one sides.
For tape width(dim W)32, 44 and 56mm pilot holes are provided on both sides.



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 0.5Pitch 1.0H ZIF/前载式
DECIMALS:	ANGLES:		PAR FPC-0.5FX-NPWBH10
.X: ± 0.30	.X': $\pm 5^\circ$		DWN
.XX: ± 0.20	.XX': $\pm 2^\circ$		CHKD
.XXX: ± 0.05	.XXX': $\pm 1^\circ$	CUSTOMER COPY	APVD
		SCALE 1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A