

M12 Wanddurchführung 5pol./B-kod.



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 330 1300
Specification	M12 Wanddurchführung 5pol./B-kod.
HARTING eCatalogue	https://b2b.harting.com/21033301300

Identification

Category	Accessories
Series	Circular connectors M12
Connector 1	M12 B-coding
	Female
	5 poles
Type of accessory	Panel feed through

Version

Gender	Male
Coding	B-coding

Technical characteristics

Rated current	4 A
Rated voltage	60 V
Limiting temperature	-25 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP67 mated condition
Thickness of the panel	2 ... 5 mm

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Brass



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 61076-2-101
----------------	-----------------

Commercial data

Packaging size	1
Net weight	25 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140137875
ETIM	EC002943
eCl@ss	27440292 Connector component (accessories)