

Actuator

45-
2131.2260.000



<https://eao.com/p/45-2131.2260.000>

Your product:



45-2131.2260.000 Actuator

FRONT

Front dimension:	Ø 29,5 mm
Front bezel colour:	Silver
Front bezel material:	Metal
Front form:	round

MOUNTING

Design:	raised
Mounting type:	Panel mounting
Mounting cut-out:	Ø 22.3 mm

OPERATING-/INDICATION PART

Lens illumination:	non illuminative
Lens colour:	Blue
Lens shape:	flush
Lens material:	Plastic
Lens optics:	opaque

MECHANICAL CHARACTERISTIC

Weight:	0.042 kg
Switching action:	Momentary
Switching system:	Slow-make switching element
Mechanical lifetime:	500 000 cycles of operation

Operating frequency: Max. 3 600/h

AMBIENT CONDITION

IP front protection: IP66, IP67, IP69K

Operating temperature: – 25 °C ... + 70 °C

Storage temperature: – 40 °C ... + 80 °C

Climate resistance: During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

Shock resistance: According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

Vibration resistance: According to IEC 60068-2-6: 20 ... 500 Hz: 5 g

CERTIFICATE

RoHS: RoHS compliant

REACH: REACH compliant


OTHER

Housing colour: Silver


Housing material: Metal

Short Description: Actuator, Ø 22.3 mm, Ø 29,5 mm, flush, non illuminative, Blue, Plastic, opaque, round, Silver, Metal, Momentary, IP66, IP67, IP69K

Wiring diagrams:



Mounting cut-outs:



Dimension drawings:

