



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Wire Size/AWG	26 - 22
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	1.00 - 12.60 mm
Size	2T
Series	T - Small Outdoor keyed

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/ega-2t-312-cym.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

R (max)	6.1 mOhm
Rated current	7 A
Vtest (contact-contact)	1650 V (AC), 2350 V (DC)
Vtest (contact-shell)	2000 V (AC), 2850 V (DC)
Contact retention	22 N
Contact Type	Crimp
Max. Conductor	0.34 mm ² (AWG 22)
Min. Conductor	0.14 mm ² (AWG 26)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	26 - 22
Gender	Standard

Form & Material

Shell style / Model id	EG - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	A: 2 keys (alpha=30, plug: male contacts, receptacle: female contacts)
Colour	Grey

Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Temperature range	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Resistance to vibration	15 g [10 Hz - 2000 Hz]
Shock Resistance	100 g [6 ms]
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/ega-2t-312-cym.html


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Jacket cable outside diameter [mm]

1.00 - 12.60 mm

Drawings



Dimensions

	A	B	e	E	L	M	N	S1	S2
mm.	18.5	19.6	M15x1.0	13.5	23.6	1.8	24.6	13.5	17
in.	0.73	0.77		0.53	0.93	0.07	0.97	0.53	0.67

Recommended By Lemo

Accessories

Replacement contact [EGG.2B.655.ZZM](#)

Compatible cap [BRE.2T.200.CAZ](#)

Tools

Positionner [DCE.91.072.BVM](#)



Extraction tool [DCC.07.04B.LAG](#)

Crimp tool [DPC.91.701.V](#)

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/ega-2t-312-cym.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.12.T22.070QGZE	TPR (medical)	Grey	
CMN.12.T28.054PGZE		grey	
CMN.12.T28.054PNZE			
112240	PTFE	White	
112260	PTFE	White	
112280	PVC	Black	
12050	PVC	Black	
124080	PVC	Grey	
124084	PVC	Black	
212220	PVC	Black	
212240	PVC	Black	
212250	PVC	Grey	
212260	PVC	Black	

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/ega-2t-312-cym.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.