








THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP67.
 - * Housing: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Shield: Zinc Alloy, Nickel Plated.
 - * Screw Nut: Copper Alloy, Nickel Plated.
 - * O-Ring1: Viton, Green.
 - * O-Ring2: EPDM, Black.
 - * For Panel Thickness Max 4.5mm.
 - * Nut Torque: 4~6 kgf.cm.

UNIT:mm				TITLE M8 5Pin Panel F Conn. F Pin			Amphenol LTW 安費諾亮泰企業股份有限公司			ITEM NO 8A-05PFFS-SH7001		DRAWN BY Tony_leng		DATE 2013-10-22				
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°				SCALE 3:1		SIZE A4				SHEET 1 OF 1		DWG NO 8A-05PFFS-SH7001		CHECKED BY Jimmy		DATE 2013-10-22		
				REV. A		WC-REV. A.1				QC:Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2013-10-22		