

## Han 6HvE-HBM-double lever



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han Hv E®
Type of hood/housing	Bulkhead mounted housing
Type	Low construction

### Version

Size	16 B
Locking type	Double locking lever
Han-Easy Lock®	Yes
Field of application	Special hoods/housings for Han Hv E® screw terminal

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)

## Material properties

Material (seal)	NBR
Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

## Commercial data

Packaging size	1
Net weight	114.62 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140053083
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors