


FPC/FFC Connector to DIP Adapter (0.40 mm pitch, 30 pins or less)


REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		1.00				
A2		3.00				
B		2.50				
C		0.20				
B2		4.00				
C2		17.80				
D		0.20				
E		0.40				
F					0.300	
G					0.100	
H					0.025	

Top View (SMT Footprint)




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)