



SPECIFICATIONS

Current Rating:3.0AMP

Contact Resistance:10mΩ Max

Dielectric Strength:Min 1000V RMS

Operation Temperature:-40°c to +105°c




Contact Material:Brass

Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PPS


Soldering Temperature: 260°C±5° 5S



Ordering Information

3610 30 2 XX S XX 119 XX

No.of Pins Per Row 2-40
Contact Plating
G1:Gold Flash
G3:2U" Gold
G4:3U" Gold
G5:5U" Gold
G6:10U" Gold
G7:15U" Gold
Length 119=11.96mm
Stream code



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

A					OPERATION		DRAW	Wei Chen	21.04.01	SCALE	FIT	JILN® 深圳市锦凌电子有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992	
					X.X	±0.30				UNIT	mm		
					X.XX	±0.20	CHECK			SIZE	A4	PART NO.	3610302XXSXX119XX
	A0	2021.04.01	NEW DRAWING		X.XXX	±0.10				SHEET	1/1		
	REV	DATE	MODIFICATION DESCRIPTION		CHANGE		APPROVE			PROJ.	◆	TITLE:	2.54x3.0 双排双头针 L=11.96上针0.6下针0.5
	1	2	3	4									