










| REV. | ECN NO.    | DATE       | SIGN   | DESCRIPTION                   |
|------|------------|------------|--------|-------------------------------|
| B    | LEN1370007 | 2013-07-08 | Cary   | Change Note & Panel Cut-out   |
| C    | LEN13A0048 | 2013-10-15 | Raison | Modify Jack PN,Note Panel THK |
| D    | LEN1610154 | 2016-01-08 | Ruru   | Change Note                   |



Tapping Use Bottoming Type, Tap #3





Blind-Hole



Effective Depth of Thread


PE BAG



Note:

- \*  $\varnothing$  Important Dimension
- \* Waterproof Rate: IP67 Unmated
- \* Housing: Nylon+GF, BLACK
- \* RJ45 Jack: Cat 5e, Shield
- \* Gasket: Silicone, UL 94V-0, Black
- \* Screw: M3.0x L=8.0mm
- \* Contact: Phosphor Bronze, Gold Flash
- \* Screw torsion value range: 1.5~2kgf-cm
- \* Temperature Range: -40°C to 105°C
- \* All Parts Should Meet RoHS Compliant.

UNIT:mm



TOLERANCE  
.X ±0.25  
.XX ±0.1  
.XXX ±0.05  
ANGLES ±1°

TITLE  
RJ45 ODVA,PANEL,FRONT LOCK  
UNMATED WATERPROOF

SCALE  
1:1

SIZE  
A4

SHEET  
1 OF 1

REV.  
D

WC-REV.  
A.3

$\varnothing$  Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

|                               |                     |                    |
|-------------------------------|---------------------|--------------------|
| ITEM NO<br>ROP-5SPFFH-TSU7001 | DRAWN BY<br>Ruru    | DATE<br>2016-01-08 |
| DWG NO<br>ROP-5SPFFH-TSU7001  | CHECKED BY<br>Rita  | DATE<br>2016-01-08 |
| CUSTOMER<br>ALTW              | APPROVED BY<br>Lisa | DATE<br>2016-01-08 |

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.