



SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Copper Alloy



Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 260°C±5°C 5S



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

2271 02 XX X N XX M U X XX

No.of Pins Per Row 02~40P	Insulator Option C=BK-PA6T E=BK-PA9T F=BK-LCP	Contact Plating G1:Gold Flash G2:1.5u" Gold G3:2u" Gold G4:3u" Gold G5:5u" Gold G6:10u" Gold G7:15u" Gold G8:30u" Gold S0:Gold Flash/Tin SN:Tin	Packing O=PE Bag A=Tray T=Tube P=Tube+Cap R=Reel+Cap M=Reel+Mylar	code stream 01~99
---------------------------------	---	---	---	----------------------



OPERATION

DRAW

yiyusheng

20.09.25

SCALE

FIT

JILN® 深圳市锦凌电子有限公司
SHENZHEN JINLING ELECTRONICS CO.,LTD

Tel: 86-755-27483253 Fax: 86-755-2997-5588

X.X

±0.30

X.XX

±0.20

X.XXX

±0.10

Angle

±3°

DIM

TOL

APPROVE

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

Φ

TITLE:

PART NO.

227102XXXXXXMUMXX

2.54PF H7.1mm 2xNpin SMT

A0

2020.09.25

NEW DRAWING

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9