

[Skip to content](#)



Tyco Electronics

Our commitment. Your advantage.



• [Products](#)

- [By Type](#)
 - [Connectors](#)
 - [Electromechanical Components](#)
 - [Electronic Modules](#)
 - [Fiber Optics](#)
 - [Filters](#)
 - [Identification & Labeling](#)
 - [Passive Components](#)
 - [Power Sources](#)
 - [RF & Microwave Products](#)
 - [Tooling Products](#)
 - [Touch Screen Displays](#)
 - [Tubing, Molded and Harnessing Products](#)
 - [Wire, Cable and Cable Assemblies](#)
 - [List all product types...](#)
- [By Industry](#)
 - [Aerospace & Defense Products](#)
 - [Appliance](#)
 - [Automotive](#)
 - [Communications](#)
 - [Computer & Consumer Electronics](#)
 - [Industrial & Commercial](#)
 - [Instrumentation & Medical](#)
- [By Brand](#)
- [A to Z](#)
- [Product News](#)

• [Documentation](#)

- [Find Documents & Drawings](#)
- [Find CAD Models](#)
- [SPICE/Electrical Models](#)
- [NAFTA Certificate of Origin](#)
- [White Papers](#)

• [Resources](#)

- [RoHS Compliance & Alternates](#)
- [Cross Reference Products](#)
- [Compare Multiple Products](#)
- [Check Distributor Inventory](#)
- [Find Authorized Distributors](#)

• [My Account](#)

- [Sign In](#)
- [Register](#)

• [Customer Support](#)

- [Support](#)
- [RoHS Support Center](#)
- [Glossary of Terms](#)
- [eBulletin Newsletter](#)

1520213-5 Product Details



Power Toggle Switches

No Image Available



Always EU RoHS/ELV Compliant (Statement of Compliance)

1520213-5



Active

Product Highlights:

- Double Pole - Single Throw Configuration (Pole-Throw)
- Toggle Length = 17.48 m m
- Toggle Style = Baton
- Bushing Length = 11.91 mm
- Termination Type = Screw-In Terminal

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Compare Products](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Single Throw
- Termination Type = Screw-In Terminal

Electrical Characteristics:

- UL/CSA 125V Current Rating (Amps.) = 16
- UL/CSA 250V Current Rating (Amps.) = 8
- UL/CSA 125V Horse Power Rating (hp) = 1.00

Housing Related Features:

- Toggle Length (m m [in]) = 17.48 [0.688]
- Toggle Style = Baton

Configuration Related Features:

- Bushing Length (mm [in]) = 11.91 [0.469]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Alcoswitch