



SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃

Contact Material:Copper Alloy





Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PBT

Max.Processing Temp: 230℃±5℃ 5S

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

2285 01 XX X N XX S Y X XX

No.of
Pins
Per Row
02~40P

Insulator Material
Option
A=BK-PBT
C=BK-PA6T
E=BK-PA9T
F=BK-LCP

Contact Plating
G1:Gold Flash
G2:1.5u" Gold
G3:2u" Gold
G4:3u" Gold
G5:5u" Gold
G6:10u" Gold
G7:15u" Gold
G8:30u" Gold
S0:Gold Flash/Tin
SN:Tin

Packing code stream
0=PE Bag 01~99
A=Tray
T=Tube
P=Tube+Cap
R=Reel+Cap
M=Reel+Mylar

Dimension antitheses list	
ITEM	PC
Standard	3.20

OPERATION

DRAW

RICH LIN

22.09.15

SCALE

FIT

X.X

±0.30

X.XX

±0.20

X.XXX

±0.10

Angle

±3°

DIM

TOL

CHECK

APPROVE

UNIT

SIZE

SHEET

PROJ.

mm

A4

1/1

◆

JILN® 深圳市锦凌电子有限公司

SHENZHEN JINLING ELECTRONICS CO.,LTD

Tel: 86-755-27483253 Fax: 86-755-2997-5588

PART NO.

228501XXXXXXSYXXX

TITLE:

2.54PF H8.5mm 1xNpin 180° W2.5mm

A0

2022.09.15

NEW DRAWING

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9