



SPECIFICATIONS

Current Rating:3.0AMP

Contact Resistance:10mΩ Max

Dielectric Strength:Min 1000V RMS

Operation Temperature:-40°C to +105°C


Contact Material:Brass

Contact Plating:Au Over Ni



Insulator Material:Polyester(UL94V-0)

Standard: PPS

Soldering Temperature: 260°C±5° 5S




注: 整条总长+0.5



Ordering Information

3612 28 1 XX S G1 100 0X

No. of Pins: 01-40P
Contact SN: Tin
Plating: G1: Gold Flash
Length: 100=10.0mm
Serial code



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

				OPERATION		DRAW	yiyusheng	18.12.13	SCALE	FIT	JILN ® 深圳市锦凌电子有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-27483253 Fax: 86-755-2997-5588	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4		
				X.XXX	±0.10				SHEET	1/1	PART NO.	3612281XXSXX1000X
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	Angle ±3°	APPROVE			PROJ.	1/1	TITLE:	2.0x2.8双头针 1xNpin 180° L=10.0(针尖0.5)
					DIM TOL							