

Accessories
DFFC 0.2-0.35 ZRV1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Spring connection with tension clamp Technology

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

Type	DFFC 0.2-0.35 ZRV1.5
Order No.	1705310000
Version	Accessories, Crimp contact, Rated cross-section: 1.5 mm ² , Crimp contact, Direct mounting
GTIN (EAN)	4008190948573
Qty.	500 pc(s).

Accessories

DFFC 0.2-0.35 ZRV1.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.21 g
------------	--------

Material data

Material	Plastic	Colour code	silver
----------	---------	-------------	--------

System specifications

Version	for holding 0.2 ... 0.35 mm ²
---------	--

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Conductors for clamping (rated connection)

Type of connection	Crimp contact
--------------------	---------------

Rating data

Rated cross-section	1.5 mm ²
---------------------	---------------------

Classifications

ETIM 3.0	EC000897	ETIM 4.0	EC000897
ETIM 5.0	EC000897	ETIM 6.0	EC000796
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-18
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20
eClass 8.1	27-14-11-20	eClass 9.0	27-44-02-04
eClass 9.1	27-44-02-04		

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of the Manufacturer
Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP