

Han-INOX 3A-HBM-DL-C



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 003 0306
Specification	Han-INOX 3A-HBM-DL-C
HARTING eCatalogue	https://b2b.harting.com/19440030306

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	 Straight With metal cover With seal

Version

Size	3 A
Locking type	Single locking lever
Field of application	Hoods/housings for harsh environments
Details	for mounted female insert or for mounted Han-Brid® insert
Pack contents	With seal screw

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Stainless steel
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	73.8 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140163645
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors