





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	

- 规格 Specification:
- 1.额定值 Rating:8A 125/250VAC
 - 2.接触电阻 Contact resistance:≤30 mΩ
 - 3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
 - 4.电气寿命 Electronics life:> 10000 cycles
 - 5.操作力 Operation force:500±200gf
 - 6.所有材料符合Rohs要求 All materials are Rohs compliant

- PART NO.:
- SS-08 22 S L-XX R 2 X X
- ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩
- ① SS: 立式拨柄开关;
 - ② 08: 额定值8A;
 - ③ 22: 双排两档;
 - ④ S: 焊线端子;
 - ⑤ L: 平柄;
 - ⑥ XX: 拨柄高度H: 3~10mm;
 - ⑦ R: 带锁环外壳;
 - ⑧ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2; 3: 端子焊脚规格TYPE-3;
 - ⑨ X: 拨柄颜色: B-黑色; W-白色; R-红色
 - ⑩ X: 主体颜色: B-黑色; W-白色; R-红色



ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

	DESIGN	桑 葚	VIEW: 	MODEL TYPE: SLIDE SWITCH			
	CHECKED			UNIT: mm/in	PART NO.: SS-0822SL-XXR2XX		
	APPROVED			SIZE: A4	DWG NO.:		
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE	PAGE	REVISION	
				N/A	1/1	A0	